



**Lewatit® DW 630** is a macroporous, monodisperse, polystyrene-based strongly basic anion exchange resin (type I). The resin has been thoroughly washed with sulfuric acid and water to assure potable water purity grade.

**Lewatit® DW 630** will not significantly exchange any major water constituents (Cl<sup>-</sup>, HCO<sub>3</sub><sup>-</sup>, NO<sub>3</sub><sup>-</sup>) because it is loaded with sulphate, which has the highest selectivity among these anions. Therefore the water composition will not be changed except the removal of target impurities.

On account of its fast kinetics, high total capacity, good chemical stability, osmotic properties and porosity **Lewatit® DW 630** is especially suitable for:

- removal of natural sulfate and carbonate complexes of uranium from potable water safely below rest concentrations below 10 ppb
- removal of natural organic matter (NOM) such as humic acids, fulvic acids, organic building blocks, carboxylic
  acids from potable water

Potable water approval certifications are country specific and available as manufacturer's declaration upon request.

In case **Lewatit® DW 630** is used for potable water treatment a special start-up procedure has to be applied. This information is available upon request.

The special properties of this product can only be fully utilized if the technology and process used correspond to the current state-of-the-art. Further advice in this matter can be obtained from Lanxess Corporation.

This document contains important information and must be read in its entirety.

Previous Edition: 2024-09-04

Edition: 2025-05-19







## Common Description

Delivery form	Sulfate
Functional group	Quaternary amine, type 1
Matrix	styrenic
Structure	macroporous
Appearance	beige, opaque

## **Specified Data**

Uniformity coefficient		max.	1.1
Mean bead size	d50	mm	0.62 (+/- 0.05)
Total capacity (delivery form)		min. eq/L	1.1

This document contains important information and must be read in its entirety.

Edition: 2025-05-19 Previous Edition: 2024-09-04







### Typical Physical and Chemical Properties

		Metric Units	
Bulk density for shipment	(+/- 5%)	g/L	650
Density		approx. g/mL	1.1
Water retention (delivery form)		approx. weight %	58-63
Volume change (during exhaustion)		max. approx. %	16
Stability pH range			0-14
Stability temperature range		°C	1-80
Storability temperature range		°C	-20 - +40

### Operation

		Metric Units	
Operating temperature		max. °C	80
Operating pH range	during exhaustion		6-8
Bed depth for single column		min. mm	1000
Back wash bed expansion per m/h (20°C)		%	40
Specific pressure loss (15°C)		kPa*h/m²	0.75
Max. pressure loss during operation		kPa	300
Specific flow rate		max. BV/h	5-50
Freeboard	during backwash	min. vol. %	80-100

### Regeneration

		Metric Units	
H₂SO₄ regeneration	concentration	approx. wt. %	10
H₂SO₄ regeneration	quantity co-current	min. g/L resin	250-350
NaCl regeneration	concentration	approx. wt. %	8-12
NaCl regeneration	quantity co-current	min. g/L resin	150-350
NaCl regeneration	quantity counter-current	min. g/L resin	100-200
Regeneration contact time		min. minutes	30
Slow rinse at regeneration flow rate		min. BV	5-10
Fast rinse at service flow rate		min. BV	10-20

This document contains important information and must be read in its entirety.

Edition: 2025-05-19 Previous Edition: 2024-09-04







### Additional Information & Regulations

PRODUCT SAFETY INFORMATION REQUIRED FOR SAFE USE OF PRODUCTS MENTIONED HEREIN IS NOT INCLUDED IN THIS DOCUMENT. BEFORE HANDLING ANY PRODUCT, ALWAYS READ PRODUCT AND SAFETY DATA SHEETS AND CONTAINER LABELS FOR SAFE USE, PHYSICAL AND HEALTH HAZARD INFORMATION.

### Safety precautions

Strong oxidants, e.g. nitric acid, can cause violent reactions if they come into contact with ion exchange resins.

#### **Disposal**

In the European Community Ion exchange resins have to be disposed, according to the European waste nomenclature which can be accessed on the internet-site of the European Union.

### Storage conditions

It is recommended to store ion exchange resins at temperatures above the freezing point of water under roof in dry conditions without exposure to direct sunlight. If resin should become frozen, it should not be mechanically handled and left to thaw out gradually at ambient temperature. It must be completely thawed before handling or use. No attempt should be made to accelerate the thawing process.

#### Storage time

The recommended storage time for this product is explained in the technical document "Technical guidelines on the storage of Lewatit® ion exchange resins" available for download on our website. Please use the following link for more information: https://lanxess.com/en/products-and-brands/brands/lewatit/literature

#### **Packaging**

The experience has shown that the packaging stability for reliable resin containment is limited to 24 months under the storage conditions described within the product safety information. It is therefore recommended to use the product within this time frame; otherwise the packaging condition should be checked regularly.

This document contains important information and must be read in its entirety.

Previous Edition: 2024-09-04

Edition: 2025-05-19







Head Office: 54/18 Bui Quang La, An Hoi Tay Ward, HCMC, Vietnam

Branch Office: 77 Dong Hung Thuan 10B, Dong Hung Thuan Ward, HCMC, Vietnam

Phone: (028) 6258 5368 - (028) 6291 9568 Email: info@atswatertechnology.com Website: www.atswatertechnology.com

The manner in which you use and the purpose to which you put and utilize our products, technical assistance and information (whether verbal, written or by way of production evaluations), including any suggested formulations and recommendations are beyond our control. Therefore, it is imperative that you test our products, technical assistance and information to determine to your own satisfaction whether they are suitable for your intended uses and applications. This application-specific analysis must at least include testing to determine suitability from a technical as well as health, safety, and environmental standpoint. Such testing has not necessarily been done by us. Unless we otherwise agree in writing, all products are sold strictly pursuant to the terms of our standard conditions of sale. All information and technical assistance is given without warranty or guarantee and is subject to change without notice. It is expressly understood and agreed that you assume and hereby expressly release us from all liability, in tort, contract or otherwise, incurred in connection with the use of our products, technical assistance, and information.

Any statement or recommendation not contained herein is unauthorized and shall not bind us. Nothing herein shall be construed as a recommendation to use any product in conflict with patents covering any material or its use. No license is implied or in fact granted under the claims of any patent.

LANXESS Corporation
111 RIDC Park West Dr
12275-1112 Pittsburgh-Allegheny

+1-800-678-0020 lewatit@lanxess.com

www.lanxess.com www.lpt.lanxess.com

This document contains important information and must be read in its entirety.

Edition: 2025-05-19 Previous Edition: 2024-09-04

