

**Lewatit® MonoPlus MP 64** is a weakly basic, macroporous anion exchange resin with beads of uniform size (monodisperse) based on a styrene-divinylbenzene copolymer. The monodisperse beads are chemically and osmotically highly stable. The optimized kinetics lead to an increased operating capacity compared to ion exchange resins with heterodisperse bead size distribution.

**Lewatit® MonoPlus MP 64** is especially applicable for:

- » the demineralization of water for industrial steam generation in combination with strong basic ion exchangers like **Lewatit® MonoPlus M 500** especially recommended for Lewatit WS System
- » the treatment of electroplating rinse waters
- » the demineralization of water with a high concentration of humic acids and other organic substances to protect the strong basic anion exchanger from fouling

**Lewatit® MonoPlus MP 64** adds special features to the resin bed:

- » high exchange flow rates during regeneration and loading
- » an excellent utilization of the total capacity
- » a low demand for rinse water
- » homogenous throughput of regenerants, water and solutions; therefore an homogeneous working zone
- » a nearly linear pressure drop gradient for the whole bed depth; therefore an operation with higher bed depth possible

The special properties of this product can only be fully utilized if the technology and process used correspond to the current state-of-the-art. Further advice in this matter can be obtained from Lanxess Corporation.

# PRODUCT INFORMATION

## LEWATIT® MonoPlus MP 64



### Common Description

Delivery form	Free base/Cl <sup>-</sup>
Functional group	tertiary amine/ quaternary ammonium
Matrix	styrenic
Structure	macroporous
Appearance	beige, opaque

### Specified Data

Uniformity coefficient		max.	1.1
Mean bead size	d50	mm	0.59 (+/-0.05)
Total capacity (delivery form)		min. eq/L	1.3

# PRODUCT INFORMATION

## LEWATIT® MonoPlus MP 64



### Typical Physical and Chemical Properties

		US Units		Metric Units	
Bulk density for shipment	(+/- 5%)	lb/ft³	38.8	g/L	620
Density				approx. g/mL	1.04
Water retention (delivery form)				approx. weight %	61-66
Volume change (free base / Cl - Cl)				max. approx. %	24
Stability pH range					0-14
Storability temperature range				°C	-20 - +40

### Operation

		US Units		Metric Units	
Operating temperature		max. °F	158	max. °C	70
Operating pH range	during exhaustion				0-8
Bed depth for single column		min. inches	31.5	min. mm	800
Back wash bed expansion per m/h (20°C)				%	21
Specific pressure loss (15°C)				kPa*h/m²	1
Max. pressure loss during operation		PSI	44	kPa	300
Specific flow rate		max. gpm/ft³	5	max. BV/h	40

### Regeneration

		US Units		Metric Units	
NaOH regeneration	concentration	approx. wt. %		approx. wt. %	2-6
NaOH regeneration	quantity co-current	min. lb/ft³	5.0	min. g/L resin	80
NaOH regeneration	quantity counter-current	min. lb/ft³		min. g/L resin	50
Regeneration contact time		min. minutes		min. minutes	30
Slow rinse at regeneration flow rate		min. gal/ft³	15.0	min. BV	2
Fast rinse at service flow rate		min. gal/ft³	29.9	min. BV	4

## Additional Information & Regulations

**PRODUCT SAFETY INFORMATION REQUIRED FOR SAFE USE OF PRODUCTS MENTIONED HEREIN IS NOT INCLUDED IN THIS DOCUMENT. BEFORE HANDLING ANY PRODUCT, ALWAYS READ PRODUCT AND SAFETY DATA SHEETS AND CONTAINER LABELS FOR SAFE USE, PHYSICAL AND HEALTH HAZARD INFORMATION.**

### **Safety precautions**

Strong oxidants, e.g. nitric acid, can cause violent reactions if they come into contact with ion exchange resins.

### **Disposal**

In the European Community ion exchange resins have to be disposed, according to the European waste nomenclature which can be accessed on the internet-site of the European Union.

### **Storage conditions**

It is recommended to store ion exchange resins at temperatures above the freezing point of water under roof in dry conditions without exposure to direct sunlight. If resin should become frozen, it should not be mechanically handled and left to thaw out gradually at ambient temperature. It must be completely thawed before handling or use. No attempt should be made to accelerate the thawing process.

### **Storage time**

The recommended storage time for this product is explained in the technical document "Technical guidelines on the storage of Lewatit® ion exchange resins" available for download on our website. Please use the following link for more information: <https://lanxess.com/en/products-and-brands/brands/lewatit/literature>

### **Packaging**

The experience has shown that the packaging stability for reliable resin containment is limited to 24 months under the storage conditions described within the product safety information. It is therefore recommended to use the product within this time frame; otherwise the packaging condition should be checked regularly.

# PRODUCT INFORMATION

## LEWATIT® MonoPlus MP 64



**Head Office:** 54/18 Bui Quang La, An Hoi Tay Ward, HCMC, Vietnam  
**Branch Office:** 77 Dong Hung Thuan 10B, Dong Hung Thuan Ward, HCMC, Vietnam  
**Phone:** (028) 6258 5368 – (028) 6291 9568  
**Email:** [info@atswatertechnology.com](mailto:info@atswatertechnology.com)  
**Website:** [www.atswatertechnology.com](http://www.atswatertechnology.com)

The manner in which you use and the purpose to which you put and utilize our products, technical assistance and information (whether verbal, written or by way of production evaluations), including any suggested formulations and recommendations are beyond our control. Therefore, it is imperative that you test our products, technical assistance and information to determine to your own satisfaction whether they are suitable for your intended uses and applications. This application-specific analysis must at least include testing to determine suitability from a technical as well as health, safety, and environmental standpoint. Such testing has not necessarily been done by us. Unless we otherwise agree in writing, all products are sold strictly pursuant to the terms of our standard conditions of sale. All information and technical assistance is given without warranty or guarantee and is subject to change without notice. It is expressly understood and agreed that you assume and hereby expressly release us from all liability, in tort, contract or otherwise, incurred in connection with the use of our products, technical assistance, and information.

Any statement or recommendation not contained herein is unauthorized and shall not bind us. Nothing herein shall be construed as a recommendation to use any product in conflict with patents covering any material or its use. No license is implied or in fact granted under the claims of any patent.

**LANXESS Corporation**  
111 RIDC Park West Dr  
12275-1112 Pittsburgh-Allegheny  
USA

+1-800-678-0020  
[lewatit@lanxess.com](mailto:lewatit@lanxess.com)

[www.lanxess.com](http://www.lanxess.com)  
[www.lpt.lanxess.com](http://www.lpt.lanxess.com)

This document contains important information and must be read in its entirety.

Edition: 2025-05-19  
Previous Edition: 2024-09-10